


# KemTab Advance - Art. No.: 510 845

- » For high requirements
- » Different control possibilities



## **Applications**

- » For plasma cutting up to 300 amps (short peaks 400 A)
- » For gas cutting with sheet metal up to 150 mm thick

#### **Benefits**

- » Better cut quality and less wear due to innovative design of the material support easyFRAME
- » No external follow-up costs caused by in-house production of wear parts due to easyFRAME
- » No cleaning or maintenance required on the material support as it can be easily replaced (easyFRAME)
- » Energy cost savings due to low extraction volume thanks to individual control of the extraction dampers of the segment in use
- » No mechanical influence of the cutting system in non-contact electronic-pneumatic control of the extraction dampers
- » Time and cost savings when cleaning the table due to large slag trays and thus longer cleaning intervals
- » Flexible table size design due to modular system (length, width)

### **Properties**

- » Low extraction volume
- » Standard material support or easyFRAME
- » Large slag trays
- » Various pneumatic control options of the extraction damper in the individual table segments
- » Modular design

## **Variants**

- » Extraction dampers can be controlled by various methods
- » Various material support frames
- » Various table widths and lengths

## **Technical Data**

asic data	
Module widths	1.100 mm, 1.600 mm, 2.100 mm,
	2.600 mm, 3.100 mm
Table height	700
Segment distance	515
Material support frame	EasyFrame Advance